

2024 Specification Sheet - English



PRODUCT NAME –

Page Title

Wire Cutter 25mm, Li-ion, Standard, 12V

PRODUCT SPECIFICATION –

Product Specification 1

Sub Brand : Gator

Product Specification 2

Type : Guillotine Style Cutter

Product Specification 3

Application : ACSR, Guy Strand, Steel

Product Specification 4

Cutting Edge : Hard Metal, Steel

Product Specification 5

Cutting Range : Cutter Head Opening: 1.000 IN (25.000 MM)

Product Specification 6

Cutting Range : ACSR: 636 KCMIL

Product Specification 7

Cutting Range : Guy Strand (Not EHS): 5/8 IN (16.000 MM)

Product Specification 8

Cutting Range : Ground Rod: 3/8 IN (9.000 MM)

Product Specification 9

Cutting Range : Rebar (SCH 60): 3/8 IN (9.000 MM)

Product Specification 10

Cutting Range : Wire Rope: 1/2 IN (13.000 MM)Cu

Product Specification 11

Jaw Size : .98 IN (25mm)

Product Specification 12

Overall Length : 15 IN (381mm)

Product Specification 13

Handle Type : In-line style with over molded rubber grip

Product Specification 14

Finish : Black