

**2024 Specification Sheet - English**

---

**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Equipped with Bluetooth™ Communication enabled via the Greenlee Gator Eye app. Features LED display screen communicating pressure and battery levels as well as tool diagnostics with real-time tool feedback.. Intelligent Crimping System Technology includes a pressure sensor that monitors the crimping force of each crimp and provides the operator with a visual and audible alert if the force is below specifications. State of the art 18 V Lithium Ion (Li-Ion) battery provides 70% more cycles per charge and faster cycle times. Retraction Stop Repeat (RSR) allows the operator to partially retract the ram and then the tool repeats the retraction for subsequent crimps

**PRODUCT NAME –**

---

**Page Title**

4 Ton Crimper, Li-Ion, standard, 12V

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Equipped with Bluetooth™ Communication enabled via the Greenlee Gator Eye app. Features LED display screen communicating pressure and battery levels as well as tool diagnostics with real-time tool feedback.

**Marketing Text 2**

Intelligent Crimping System Technology includes a pressure sensor that monitors the crimping force of each crimp and provides the operator with a visual and audible alert if the force is below specifications

### **Marketing Text 3**

State of the art 18 V Lithium Ion (Li-Ion) battery provides 70% more cycles per charge and faster cycle times

### **Marketing Text 4**

Retraction Stop Repeat (RSR) allows the operator to partially retract the ram and then the tool repeats the retraction for subsequent crimps

### **Marketing Text 5**

LED light provides the operator with the battery charge and tool maintenance status

### **Marketing Text 6**

Forward handle position improves tool balance

### **Marketing Text 7**

One trigger controls all tool functions

### **Marketing Text 8**

Crimping head rotates 350°

### **Marketing Text 9**

Tools automatically retract when the crimping cycle is complete

### **Marketing Text 10**

Overmolded tacky grip areas make gripping the tool easier and more comfortable

### **Marketing Text 11**

LED work light illuminates dark work areas

### **Marketing Text 12**

Greenlee battery-powered crimping tools now use bio-degradable oil

### **Marketing Text 13**

Smart chargers control the charging current, charging voltage and battery temperature to maximize battery life. Available with 120 V, 12 V or 230 V battery charger or with 120 V or 230 V corded adapter in place of batteries and charger use optional CCX Blades and adapters.

### **Marketing Text 14**

U.S. Patent #6,206,663, #6,532,790, When used with Greenlee KC12 and KA12 dies in combination with Anderson®, Blackburn®, FCI Burndy®, ILSCO®, Panduit®, Penn-Union® and Thomas & Betts® color-coded connectors, crimps on connections up to 750 kcmil are UL and cUL classified. The tools also accept all industry U type dies

### **Marketing Text 15**

These tools drive knockout punches through 5-5/8" diameter.

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Sub Brand : Gator

### **Product Specification 2**

Type : Die style crimper

**Product Specification 3**

Application : 4 Ton Crimping

**Product Specification 4**

Standard : C/US UL Listed

**Product Specification 5**

Wire Size : 8 AWG - 300 kcmil Cu

**Product Specification 6**

Wire Size : 8 AWG - 2/0 kcmil Al

**Product Specification 7**

Overall Length : 13.25 IN (337mm)

**Product Specification 8**

Crimping Force : 7,900 lbs. (35 kN)

**Product Specification 9**

Crimping Capacity : 300 kcmil (MCM) Copper

**Product Specification 10**

Crimping Capacity : 2/0 AWG Al

**Product Specification 11**

Connector Type : Color-coded lugs and splices

**Product Specification 12**

Handle Type : In-Line Style with over molded rubber grip