

SUPERPUCK RECESS

PRECISION LED LIGHTING

Enjoy energy-saving white light in a variety of attractive finishes. These LED pucks are well suited to accent and task lighting under cabinets and in other areas.





KEY FEATURES

Available in 2 wattages Extra-low profile Ideal for highlighting display cabinets



MODEL

4001 1.6W Single puck, 3000°K, 168 Lumens 4001HP 2.9W Single puck, 3000°K, 298 Lumens

SPECIFICATIONS

- 12V DC LED driver required.
- Over 50,000 hours of service life.
- 12" (30 cm) input lead with guick connector.
- 24" (61 cm) interconnection harness included.
- · Warm white light output.
- 90 CRI.
- · Superior LED performance and lifespan.
- Smooth 360°-wide spread.
- · Minimal heat emission.
- Heat sink and thermal protection.
- · Steel and aluminum construction.
- Frosted glass lens.
- Dimmable with most low-voltage electronic dimmers when used with DALS dimming power supply.
- IC certification (suitable for direct contact with insulation).

INSTALLATION

- · For recessed installation only, in any direction.
- · Ideal for accent lighting inside or under any cabinet, shelf or display.
- A variety of power supplies and installation accessories available.
- Approved for insulated ceilings.

FINISH

ВK Black WH White Satin nickel SN

POWER SUPPLIES — PLUG-IN


ETR-LED10WPI 12VDC/10W class 2 LED driver ETR-LED24WPI 12VDC/24W class 2 LED driver

POWER SUPPLIES — HARD-WIRED

BT06DIMLED-IC 6W dimmable LED hardwire driver BT12DIMLED-IC 12W dimmable LED hardwire driver BT24DIMLED-IC 24W dimmable LED hardwire driver 36W dimmable LED hardwire driver BT36DIMLED BT48DIMLED 48W dimmable LED hardwire driver

ACCESSORIES

4000E-24 24" (61 cm) extension cord 4000E-60 60" (152.4 cm) extension cord 4000HRNS-24 24" (61 cm) interconnection harness



ORDERING EXAMPLE

4001HP-BK

Would order a 4001 single high-power puck with a 1.6W LED array with 298 Lumens at 3000°K in a black finish.