
Camber

The innovation of this design comes from its recessed installation. This step light will be perfectly integrated into stairs and can also be used on decks.



Model	Size	Watts	Delivered lumens	CRI	Color °T	Voltage
LEDSTEP005D-CC	4-3/4"	3 W	90 lm	90	2200, 2700, 3000, 3500, 4000 K	120 V

Specifications

Die-cast aluminum housing
 Over 50,000 hours of service life
 Switch-selectable CCT: 2200 K/2700 K/
 3000 K/3500 K/4000 K
 Integrated dimmable driver
 Suitable for wet locations
 Install in standard electrical junction box
 Refer to website for dimmer compatibility
 Ideal operating temperature:
 -20° to 40° C
 5-year warranty

Finish

- **BK** Black
- **WH** White

Note

Other color temperatures, finishes, and voltage options are available but may require minimum order quantities (MOQs) and longer lead times. Please contact your DALs representative for more information.

LEDSTEP005D-CC

