



Pass and Seymour
2-Gang Thermost Wall Plate, 2 Toggle Switch Openings, White
Part No. SP2W



Smooth Wall Plate 2-Gang 2-toggle

Features & Benefits

Molded of non-combustible mar-proof material.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Resistant to discoloration, grease, oil, solvent, and moisture.

For covering patents, see www.legrand.us/patents.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Individually wrapped with color-matching screws.

Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007681567
Country Of Origin	Mexico	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Toggle Switch
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Technical Information

Thickness	0.07 in	Number of Gangs	2
-----------	---------	-----------------	---

Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
----------------	--------	---------------	---------------

Orientation	Vertical
-------------	----------
