

Smooth Metal Wall Plate 4-Gang Toggle 430 Stainless Steel



Features & Benefits

| | |
|--|---|
| Type 430 Stainless Steel, magnetic: .032" nominal thickness. | Brushed finish. |
| Less corrosion-resistant than Type 302, but ideal for general service in high abuse applications in industrial plants, commercial, and industrial buildings. | Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel. |
| Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide. | Packaged in protective film, with finish-matching screws. |
| Variety of special plated finishes. | Paintable to match plastic plates. |
| Can be silk-screened or engraved, and custom punched with over 300 opening styles. | For covering patents, see www.legrand.us/patents . |

Specifications

General Info

| | | | |
|-------------------|-------------------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Stainless Steel |
| Finish | Metallic | UPC Number | 785007657982 |
| Country Of Origin | United States | Wall Plate Size | Standard Size |
| Wall Plate Type | Toggle Switch | Application Sector | Commercial, Residential |
| Warranty Type | 1-Year Limited Warranty | Type | Wall Plate |

Dimensions

| | | | |
|------------------|----------|------------------|--------|
| Product Width US | 8.125 in | Product Depth US | 0.2 in |
|------------------|----------|------------------|--------|

| | |
|-------------------|--------|
| Product Height US | 4.5 in |
|-------------------|--------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143223 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------|----------|-----------------|---|
| Thickness | 0.032 in | Number of Gangs | 4 |
|-----------|----------|-----------------|---|

| | | | |
|----------------|--------|---------------|---------------|
| Indoor/Outdoor | Indoor | Mounting Type | Strap Mounted |
|----------------|--------|---------------|---------------|

| | |
|-------------|----------|
| Orientation | Vertical |
|-------------|----------|
