



3/4" HEX CHISELS

Tip Type	Style	Application	Size	Part No.
	Clay Spade	Digs up clay, hard-packed gravel and dirt	4-1/2" x 16-3/4"	48-62-3040
	Ground Rod Driver	Drives soft ground rods	9-3/4"L - 5-8" & 3/4" Rod Diameter	48-62-3070
	Tamper Shank	Used to mount tamper plate	12"	48-62-3065
	Tamper Plate	Compacts dirt, tamps asphalt	5" x 5"	48-62-3060

1-1/8" HEX



1-1/8" HEX DEMOLITION STEEL



1-1/8" HEX DEMOLITION STEEL

Tip Type	Style	Application	Size	Part No.
	Moil Point	Starts holes in concrete slabs, general chipping and breaking	16"	48-62-4001
	Moil Point		20"	48-62-4000
	Narrow Chisel	General chipping and breaking	16"	48-62-4006
	Narrow Chisel		20-1/2"	48-62-4005
	Scaling Chisel	Cleans concrete, scale, rust, cuts troughs and some asphalt	3" x 20-1/2"	48-62-4010
	Asphalt Cutter	Cuts asphalt or hard ground (DO NOT use for concrete)	5" x 17-1/2"	48-62-4020
	Clay Spade	Digs up clay, hard-packed gravel and dirt	5-1/2" x 20"	48-62-4030
	Ground Rod Driver	Drives soft ground rods	15-1/2"L x 3"	48-62-4045
	Spike & Pin Driver	Drives anchoring pins for concrete forms	14-1/2"	48-62-4040
	Tamper Shank	Used to mount tamper plate	6" x 6"	48-62-4060

1-1/8" HEX DEMOLITION STEEL

Tip Type	Style	Application	Size	Part No.
	Tamper Plate	Compacts dirt, tamps asphalt (Use with 48-62-4060)	6" x 6"	48-62-4050
	Tamper Plate		8" x 8"	48-62-4055
	Tent Stake Driver – Head Only	Drives in large tent stakes (Use with 48-62-4060)	5-1/2" L / 3-1/2" OD / 2-3/4" ID	48-62-4061

CARBIDE HAMMER DRILL BITS

OVERVIEW

MILWAUKEE® Carbide Hammer Drill Bits use sharpened carbide, delivering up to 5X life in concrete and up to 2X faster drilling. Engineered with a precision ground tip, these bits will deliver faster starts and less walking in concrete, brick, block and masonry. Wide flute design removes dust faster, reducing heat and delivering more holes per charge. The extended life of the MILWAUKEE® Carbide Hammer Drill Bits provides the ideal solution in concrete, brick and block for cordless and corded hammer drill/drivers.

FEATURES

- Up to 5X life in concrete
- Up to 2X faster versus standard masonry bits
- Durable Carbide Tip: Longer life in concrete and hard aggregate



CARBIDE HAMMER DRILL BITS

Diameter	Usable Length	Length	Shank Type	1 Pack	5 Pack	25 Pack
1/8"	2"	3-1/2"	SHOCKWAVE Impact Duty™	48-20-9000	–	48-20-9100
5/32"	4"	6"	SHOCKWAVE Impact Duty™	48-20-9001	48-20-9155	48-20-9101
3/16"	2"	4"	SHOCKWAVE Impact Duty™	48-20-9005	–	48-20-9105
3/16"	4"	6"	SHOCKWAVE Impact Duty™	48-20-9006	48-20-9157	48-20-9106
7/32"	4"	6"	SHOCKWAVE Impact Duty™	48-20-9009	–	–
1/4"	2"	4"	SHOCKWAVE Impact Duty™	48-20-9010	–	48-20-9110
1/4"	4"	6"	SHOCKWAVE Impact Duty™	48-20-9011	48-20-9162	48-20-9111
1/4"	10"	12"	3-Flat	48-20-9012	–	–
5/16"	4"	6"	SHOCKWAVE Impact Duty™	48-20-9016	–	48-20-9116
5/16"	8"	10"	3-Flat	48-20-9018	–	–
5/16"	10"	12"	3-Flat	48-20-9017	–	–
3/8"	4"	6"	SHOCKWAVE Impact Duty™	48-20-9021	–	48-20-9121
3/8"	10"	12"	3-Flat	48-20-9022	–	–
3/8"	16"	18"	3-Flat	48-20-9023	–	–
7/16"	4"	6"	SHOCKWAVE Impact Duty™	48-20-9025	–	48-20-9125
1/2"	4"	6"	SHOCKWAVE Impact Duty™	48-20-9030	–	48-20-9130
1/2"	10"	12"	3-Flat	48-20-9031	–	–
1/2"	16"	18"	3-Flat	48-20-9032	–	–
9/16"	4"	6"	3-Flat	48-20-9035	–	–