

GDL

- Glass body
- Time-delay
- 1/4" x 1-1/4"
- 1-1/2" Axial leads optional



1/16A through 8A,
250VAC,
UL Listed and
CSA Certified

10A through 15A, 125VAC,
UL Listed and CSA Certified

20A through 30A, 32VAC



STANDARD FUSE AMPERE RATINGS

Catalog Number	Ampere Rating	Volts	I.R.
N/A	1/16A	250V	1
N/A	1/10A	250V	1
N/A	1/8A	250V	1
N/A	15/100A	250V	1
N/A	175/1000A	250V	1
N/A	3/16A	250V	1
N/A	2/10A	250V	1
N/A	1/4A	250V	1
N/A	3/10A	250V	1
N/A	3/8A	250V	1
N/A	4/10A	250V	1
GDL1/2	1/2A	250V	1
GDL6/10	6/10A	250V	1
GDL7/10	7/10A	250V	1
GDL3/4	3/4A	250V	1
GDL8/10	8/10A	250V	1
GDL1	1A	250V	1
GDL1-1/4	1-1/4A	250V	2
GDL1-1/2	1-1/2A	250V	2
GDL1-6/10	1-6/10A	250V	2
GDL1-8/10	1-8/10A	250V	2
GDL2	2A	250V	2
GDL2-1/4	2-1/4A	250V	2
GDL2-1/2	2-1/2A	250V	2
GDL2-8/10	2-8/10A	250V	2
GDL3	3A	250V	2
GDL3-2/10	3-2/10A	250V	2
GDL4	4A	250V	3
GDL5	5A	250V	3
GDL6	6A	250V	3
GDL6-1/4	6-1/4A	250V	3
GDL7	7A	250V	3
GDL8	8A	250V	3
GDL10	10A	125V	4
GDL12	12A	125V	4
GDL15	15A	125V	4
GDL20	20A	32V	5
GDL25	25A	32V	5
GDL30	30A	32V	5

1. 250VAC @ 35A I.R./125VAC @ 10kA I.R.
2. 250VAC @ 100A I.R./125VAC @ 10kA I.R.
3. 250VAC @ 200A I.R./125VAC @ 10kA I.R.
4. 125VAC @ 10kA I.R.
5. 32VAC @ 300A I.R.