



Ratcheting Ferrule Square Crimper, 10 to 22 AWG Wire



The full-cycle ratcheting ferrule crimper crimps 10-22 AWG ferrule terminals. This tool features four crimping dies that surround terminals 360 degrees for a high quality square shaped crimp. The unique design provides a low effort to crimp while maintaining a high terminal pull-off force. Built in ratchet ensures full-cycle crimping for a complete uniform crimp every time. Dual layer molded grips provide high level of comfort during use.

Specifications

Type:	Ratcheting Crimper	Application:	Ferrule Terminal Crimping on Stranded Wire
Special Features:	Compressive Jaws	Material:	Steel
Handle Color:	Black/Grey	Handle Finish:	Dual-Material
Cable Size:	10-22 AWG	Connector Type:	Ferrule
Overall Length:	7" (18 cm)	Overall Height:	0.5" (1.5 cm)
Overall Width:	3" (7.6 cm)	Weight:	12.8 oz (363 g)