



## Ratcheting Ferrule Hex Crimper, 10 to 22 AWG Wire



The full-cycle ratcheting ferrule crimper crimps 10-22 AWG ferrule terminals. This tool features six crimping dies that surround terminals 360 degrees for a high quality hex shaped crimp. The unique design provides a low effort to crimp while maintaining a high terminal pull-off force. Built in ratchet ensures full-cycle crimping for a complete uniform crimp every time. Dual layer molded grips provide high level of comfort during use.

### Specifications

<b>Type:</b>	Ratcheting Crimper	<b>Application:</b>	Ferrule Terminal Crimping on Stranded Wire
<b>Special Features:</b>	Compressive Jaws	<b>Material:</b>	Steel
<b>Handle Color:</b>	Black/Grey	<b>Handle Finish:</b>	Dual-Material
<b>Cable Size:</b>	10-22 AWG	<b>Connector Type:</b>	Ferrule
<b>Overall Length:</b>	7" (18 cm)	<b>Overall Height:</b>	0.5" (1.5 cm)
<b>Overall Width:</b>	3" (7.6 cm)	<b>Weight:</b>	12.8 oz (363 g)