FLO Home™ G5

The home EV charger that keeps charging, rain or shine

Built to outlast

- **Engineered to withstand the toughest conditions.**
  100% aluminum enclosure is waterproof and corrosion-resistant (type 4X) that is capable of enduring impact.

- **Charge in the frozen tundra or the sweltering desert.**
  We operate in a wider range of temperatures from -40 °C to 50 °C.

- **We've got you covered.**
  We put our money where our mouth is and stand behind our quality with a 3-year limited warranty.

Sophisticated charging

- **Discreet design complements your home.**
  Integrated, illuminated cable holster keeps 7.6 m premium cable organized at all times.

- **Elegance meets flexibility.**
  Wiring options behind and under the station keep the design clean for your house.

Worry-free

- **Safety is infused in everything we do.**
  Integrated safety features protect against supply imbalance and overload current.

- **We're here 24/7.**
  We've got your back whether you're at home or using one of our thousands of chargers on the go.

- **Install to charge in no time flat.**
  Electricians love our easy and flexible installation that works with your unique home.

Model Number HOG50001-FL-P08

FLO Home™ G5

Technical Specifications

ELECTRICAL

Output Power	6.2 – 7.2 kW
Output Current	30 A (adjustable from 6 to 30 A)
AC Input Voltage	208-240 V @ 60 Hz
AC Input Connection	• Hardwired (must be installed by a licensed electrician) • L1, L2, G • Under & rear hardware entry options
Security Features	Integrated GFCI 20mA, 3 reset attempts at 15-minute intervals

ENVIRONMENT

Operating Temperature	-40 °C to 50 °C (-40 °F to 122 °F)

CERTIFICATION & COMPLIANCE

Certifications	• Meets all applicable UL safety standards. Certified by CSA group • UL 2231 / UL 2594 / CSA C22.2 No 280 • FCC 47 CFR Part 15

PHYSICAL

Dimensions (H x W x D)	432 mm x 193 mm x 175 mm (17" x 7.6" x 6.9")
Weight	11.18 kg (24.65 lbs)
Cable	7.62 m (25') commercial grade
Charging Connector	SAE J1772 designed to withstand 10,000+ charging cycles
Enclosure	100 % Aluminum type 4X (waterproof and corrosion proof)
Mounting	Wall bracket included
Impact Rating	IK10
Limited Warranty	3 years

Learn more
info@flo.com
1 (855) 543-8356
flo.com

Made in North America

Designed and manufactured by AddÉnergie Technologies Inc. d/b/a FLO.