

Alter series

This aluminum retrofit LED panel offers the easiest and most practical solution for upgrading your outdated recessed lighting. For style and convenience, the removable outer trim attaches with magnetic fasteners, creating a seamless look. It can be easily retrofitted into existing 4" canisters or standard octagonal junction boxes.

NEW WET RETROFIT AIR TIGHT ETL Intertek ENERGY STAR

2700k 3000k 3500k 4000k 5000k
COLOR TEMPERATURE *
T24 JA8
CERTIFIED



*Models RTJB3-CC and RTJB4-CC only

| Model | Size | Watts | Delivered lumens | CRI | Color °T | Voltage |
|-----------------|------|-------|------------------|-----|-----------------------------------|---------|
| RTJB4-3K | 4" | 9 W | 550 lm | 90 | 3000 K | 120 V |
| RTJB3-CC | 3" | 8 W | 620 lm | | 2700, 3000, 3500, 4000, 5000 K | |
| RTJB4-CC | 4" | 9 W | 565 lm | | | |

Specifications

Fits on U.S. and Canadian octagonal junction boxes
 Fire rated alternative when mounted onto a fire rated junction box
 Minimal heat emission
 Aluminum construction
 Switch-selectable CCT: 2700 K/ 3000 K/3500 K/4000 K/5000 K (models RTJB3-CC, RTJB4-CC only)
 Over 50,000 hours of service life
 Magnetic trim finish
 Air-tight certified as per ASTM E283-04
 Suitable for wet locations
 Refer to website for dimmer compatibility
 Ideal operating temperature: -20° to 40° C
 5-year warranty

Finish

○ **WH** White

Accessories




RTJB4-ACC
 4" recessed can mounting kit for RTJB4-XX - clips and E26 socket

RTJB4-TRIM-BK
 4" recessed panel trim in black



Note

Other color temperatures, finishes, and voltage options are available but may require minimum order quantities (MOQs) and longer lead times. Please contact your DALs representative for more information.

RTJB3-CC



RTJB4-XX



RTJB4-XX + RTJB4-ACC

