



Catalog Number
Notes
Type

Contractor Select™

TRUM LED Wrap

TruWrap Medium Body Flat



2" profile, linear wraparound with traditional wrap performance and modern aesthetic. Features include conduit end feed/through wire capability, captive end caps and a microprismatic polycarbonate diffuser providing uplight & widespread uniform illumination. Ideal for many applications including corridors, classrooms, break rooms, utility work areas, laundry rooms, basements and stairways.

FEATURES:

- Fully captive Microprismatic™ diffuser providing floor to ceiling illumination
- Low profile evenly illuminated diffuser offering a modern aesthetic appearance
- Conduit end feed and through-wire capable
- Adjustable lumens (3ALO) & color temperature (3CCT)
- MVOLT (120-277VAC) & 0-10V dimming to 10%



Catalog Number	UPC	Description	Nominal Lumens	Input Watts	Voltage	Color Temperature	Dimming	Pallet qty.
TRUM 48 ALO6 FMP 8SWW2 ZT MVOLT	197589468830	4' LED Wrap	4000, 5000, 6000	53W @6000LM	120-277V	3000, 4000, 5000	0-10V	75

Note: *When using 0-10v dimming with ALO options it is recommended to set the ALO to the MAX output.



Specifications

INTENDED USE:

The TruWrap LED wrap platform was designed with the renovator in mind, while compatible with new construction. It's no mystery the flexibility of the TruWrap will keep renovation simple. The platform is designed to be backwards compatible with existing legacy wraps to perfectly cover blemishes from older fixtures. Conduit end feed and through wire capability makes challenging installations a breeze. The option to adjust lumens and color temperature grants the perfect amount of light to any room. This is capped off with standard 0-10v dimming and a uniform microprismatic diffuser that offers floor to ceiling light. All this means the TruWrap shines in, hallways, laundry rooms, offices, utility work areas, and more.

CONSTRUCTION:

The LED wrap is constructed of a metal chassis with decorative captive plastic end caps. The microprismatic diffuser provides even illumination and softens the appearance of the LEDs for improved aesthetics.

OPTICS:

ALO6 8SWW2: Wraps are switchable between 4,000, 5,000, and 6,000 lumens. Wrap color temperature is switchable between 3000K, 4000K and 5000K.

80CRI

Diffuser utilizes state of the art Microprismatic technology which provides a uniformly illuminated surface with no lamp image. This also provides unmatched volumetric floor to ceiling light and a modern aesthetic.

ELECTRICAL:

Long-life LEDs, coupled with a high-efficiency driver, provide superior illumination for extended service life. 80% LED lumen maintenance at 60,000 hours (L80/60,000). Fixture mounts to recessed junction box, electrical connections must be made inside junction box.

LISTINGS:

CSA certified to US and Canadian standards. Listed for damp locations, at -4-194°F (-20-90°C).

DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at www.designlights.org/QPL to confirm which versions are qualified.

WARRANTY:

5-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at:

www.acuitybrands.com/support/warranty/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

Dimensions

All dimensions are inches (centimeters) unless otherwise indicated.

Width 8-7/8" (22.54cm)

Length 48" (121.92cm)

Depth 2-1/8" (5.4cm)

Weight 6.6lbs (3kg)

