

TECHNICAL DATA

# Fluke 325 True RMS Clamp Meter



## Key features

- True-rms AC/DC current, voltage, temperature, frequency
- Clamp meter, test leads, K-type thermocouple and soft case
- Versatile tool performs most front-line measurement tasks

## Product overview: Fluke 325 True RMS Clamp Meter

Troubleshoot problems safely and accurately

The Fluke 325 True-rms Clamp Meter is a reliable, versatile troubleshooting tool for commercial and residential electricians. Featuring a slim design for easy transport and use, and a large display for efficient troubleshooting. In addition to true-rms AC current and voltage on non-linear loads, the 325 measures:

- DC current
- DC voltage
- Temperature
- Frequency

You'll carry fewer tools in your bag and get more work done.

Covers most problems you see day-in, day-out

The 325 gives you a strong combination of measurement functions, in a tool that is reliable, easy-to-use and affordable. This

clamp meter offers True-rms AC voltage and current measurements on non-linear signals. Paired with the CAT III 600 V, CAT IV 300 V safety rating the clamp meter can also measure:

- Measures AC/DC current up to 400 A through jaw
- AC/DC voltage to 600 V using test leads
- Measures frequency from 5 Hz to 500 Hz; resistance to 40 kΩ
- Measures temperature from -10 °C to 400 °C with included K-type thermocouple
- Min/Max function records important values

Comes with a two-year warranty

## Specifications: Fluke 325 True RMS Clamp Meter

Specifications		
AC current	<b>Range</b>	40.00 A / 400.0 A
	Accuracy	2% ± 5 digits (45 Hz to 65 Hz) 2.5% ± 5 digits (65 Hz to 400 Hz)
DC current	<b>Range</b>	40.00 A / 400.0 A
	Accuracy	2% ± 5 digits
AC voltage	<b>Range</b>	600.0 V
	Accuracy	1.5% ± 5 digits
DC voltage	<b>Range</b>	600.0 V
	Accuracy	1.0% ± 5 digits
Resistance	<b>Range</b>	400.0 Ω / 4000 Ω / 40.00 kΩ
	Accuracy	1.0% ± 5 digits



Continuity		$\leq 30 \Omega$
Capacitance		0 to 100.0 $\mu\text{F}$ / 100 $\mu\text{F}$ to 1000 $\mu\text{F}$
Frequency		5.0 Hz to 500.0 Hz
AC response		True-RMS
Backlight		Yes
Data hold		Yes
Contact temperature		-10.0°C to 400.0°C (14.0°F to 752.0°F)
Min/Max		Yes
Size	<b>H x W x D (mm)</b>	207 x 75 x 34
	Max wire diameter	30 mm (600 MCM)
	Weight	283 g
Category rating		CAT III 600 V CAT IV 300 V
Warranty		Two-year

## Ordering information



### Fluke 325

Fluke 325 True-RMS Clamp Meter

Includes:

- Fluke 325 True-RMS Clamp Meter
- TL75 Test Leads
- Type K Thermocouple
- Two AAA Batteries (Installed)
- Soft Case

### Fluke 325 CAL

Fluke 325 True RMS Clamp Meter, with a traceable certificate of calibration with data from Fluke

Includes:

- Fluke 325 True-RMS Clamp Meter
- TL75 Test Leads
- Type K Thermocouple
- Two AAA Batteries (Installed)
- Soft Case
- A traceable certificate of calibration with data from Fluke

### R-FLUKE-325

Fluke 325 True RMS Clamp Meter, fully reconditioned to original factory specifications. Includes Fluke's 2 year product warranty.

#### Optional accessories

**Fluke TL75 Hard Point™ Test Lead Set**

**Fluke TL175 TwistGuard™ Test Leads**

#### Description

PVC-insulated, right-angle shrouded 4 mm (0.16 in) banana plugs

Simply twist to change the exposed probe tip length.



**Optional accessories**

**Description**

**Fluke TLK-225 SureGrip™ Master Accessory Set**

Includes all the SureGrip™ leads and probes in a handy six-pocket, roll-up pouch, along with TL224 test leads.

**Fluke insulated hand tools starter kit**

8-piece kit has the most popular screwdrivers, pliers and cutters.



**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2023 Fluke Corporation.  
Specifications subject to change without notice.  
05/2023

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**