

STF362P – CONCERTO PROGRAMMABLE

FLOOR HEATING THERMOSTAT

PROGRAMMABLE



AVAILABLE SOON



DIAL IN COMFORT FOR YOUR FEET!

The CONCERTO Programmable thermostat delivers comfort and energy savings. Thanks to its pre-programmed settings, configuration is quick and easy. Its intuitive interface and large, bright screen offer a simplified user experience with a distinctive design. Create personalized schedules to heat your home according to your needs, ensuring greater energy efficiency while keeping your feet warm.

- **SIMPLE INTERFACE AND LARGE, ILLUMINATED DISPLAY FOR INTUITIVE PROGRAMMING**
- **PRE-PROGRAMMED FOR RAPID CONFIGURATION**
- **EASY PROGRAMMING OF UP TO FOUR WEEKDAY EVENTS AND TWO WEEKEND EVENTS**
- **ENERGY MONITORING**
TRACK YOUR FLOOR'S ENERGY CONSUMPTION
- **GROUND FAULT CIRCUIT INTERRUPTER (GFCI CLASS A)**
PROTECTS USERS AND THE INSTALLATION

COLOUR

- White

FINISH

- Moulded plastic

MANUFACTURING

- Fitted with an integrated ground fault circuit interrupter (GFCI) and a test indicator light.
- Terminal block connection / DPST with 2-pole disconnects
- Floor sensor (15 ft/4.5 m) included*

POWER AND VOLTAGE

- Maximum of 1800 W @ 120 V
- Maximum of 3120 W @ 208 V
- Maximum of 3600 W @ 240 V

CONTROL

- Pre-programmed with four weekday events and two weekend events
- Option of controlling Floor temperature (F), Room temperature (R), Room with Floor limit (RF) or in Controller mode (without temperature reading)

- Possibility of setting a maximum temperature setpoint (to protect the floor and users)
- Adaptive function (Early start) – allows heating to reach the setpoint as soon as the program starts
- Temperature can be displayed in degrees Celsius or Fahrenheit

PRECISION

- Precise control of floor or ambient air temperature
- Temperature reading with thermistor

TEMPERATURE RANGE

- Floor: 5 to 40°C (41 to 104°F)
- Ambient: 0 to 40°C (32 to 104°F)

WARRANTY

- Three years

*This thermostat is also compatible with floor sensors produced by other manufacturers.

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS	VOLTAGE	AMPERAGE	FREQUENCY	GFCI
CODE	MAXIMUM	VOLTS	AMPS	HZ	MA
STF362P	1800/3120/3600	120/208/240	15	50/60	5

°STELPRO

Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website www.stelpro.com.