



# 66EV-10W

SureSlide Dimmer Switch for Electronic Low Voltage Bulbs

Decora SureSlide ELV Dimmer, 300VA-120VAC Electronic Low Voltage, 60Hz, Single Pole and 3-Way - White

Leviton Decora SureSlide® dimmers provide smooth, slide-action, full-range dimming for a variety of lamp types including Incandescent, LED, CFL and ELV. Featuring a pre-set ON/OFF switch, this device allows the user to set the desired brightness level to operate automatically with the ON/OFF function. The dimmer is designed specifically for controlling Electronic Low Voltage transformers.

Color :  White

UPC Code : 078477937037

Country Of Origin : China

### Available Colors :



Ivory



Light Almond

## Technical Information

### Product Features

**Action** : Standard ON/OFF

**Available Colors** : Ivory-I Wht-  
W Light Almond-T

**California Title 24** : Yes

**Color** : White

**Light** : None

**Load Rating** : 300VA ELV

**Load Type** : Electronic Low  
Voltage

**Ordering Notes** : White

**Preset** : Preset

**Protection** : Radio/TV Filter

**Standards and Certifications**  
: UL/CSA

**Style Name** : SureSlide

**Switch Type** : Single-Pole & 3-  
Way

**Type** : Electro-Mechanical

**Voltage** : 120 VAC

**Wallplate** : Order Separately

**Warranty** : 5-Year Limited

## Features and Benefits

- New updated look.
- Integrated linear full-range slide control for easy, precise operation.
- Features a separate ON/OFF switch that preserves the selected brightness setting.

- \_ Single pole or 3-way lighting control when used with a 3-way switch.
- \_ Slim, compact housing fits easily into a standard wallbox and is suitable for multi-gang installations.
- \_ Ability to dim and control Electronic Low Voltage transformers for a variety of light sources
- \_ Built-in radio/TV interference filter.
- \_ Can be used to comply with 2016 California Title 24, Part 6 Indoor Lighting Switching Devices and Controls
- \_ Available colors: White, Ivory and Light Almond.

**Patents\***

US7242563

This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

**SPECIFICATION SUBMITTAL**

JOB NAME: <input style="width: 95%; height: 20px;" type="text"/>	CATALOG NUMBERS: <input style="width: 45%; height: 20px;" type="text"/> <input style="width: 45%; height: 20px;" type="text"/>
JOB NUMBER: <input style="width: 95%; height: 20px;" type="text"/>	<input style="width: 45%; height: 20px;" type="text"/> <input style="width: 45%; height: 20px;" type="text"/>

**Leviton Manufacturing Co., Inc**

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S. T. Monday-Friday): +1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 · FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52) 5386- 1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2024 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to: [www.leviton.com/international/contacts](http://www.leviton.com/international/contacts)

**© 2024 Leviton Manufacturing Co., Inc.**