



Electronic Stud Finder



Electronic Stud Finder detects hidden wood and metal studs with an auto deep scan capability of up to 1-1/2-Inch. The device offers mutable audible alerts and bright LEDs across the top, clearly indicating the full width of the stud. It features an ergonomic handheld grip, HOLD mode, and withstands a 6.6-Foot (2 m) drop. Felt pads protect walls during use and a bubble vial assists with alignment.

Specifications

Type:	Electronic	Application:	Detect Metal And Wood Studs Behind Walls, Center and Edge-Finding
Special Features:	Felt Pads; Handheld Grip; Hold Mode; Mute Audible Tones; Drop Protection 6.6' (2m)	Magnetic:	No
Level Included:	Bubble-Level	Automatic Operation:	No
Audible Alert:	Yes	Detects Metal:	Yes
Detects Voltage:	No	Detects Live Wires:	No
Display:	(7) Bright Green LEDs	Scans Material:	Metal; Wood
Scan Depth:	Up to 1.5" (3.8 cm)	Overall Length:	7" (19.4 cm)
Overall Height:	4.5" (11.4 cm)	Overall Width:	2.25" (5.72 cm)
Material:	PC & PC-ABS Housing and Electronic Components	Drop Protection:	6.6' (2 m)
Batteries:	(2) AA (1.5V)	Included:	Stud Finder, (2) AA Batteries, Manual
Weight:	10.4 oz. (0.3 kg)	Battery Type:	Alkaline