



# Ceramalux Instant Restrike

## 37688-9 400W C400S51/2 Dual Arc Hp Lamp

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

### Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]

  

Light Technical	
Luminous Efficacy (rated) (Nom)	125 lm/W
Chromaticity Coordinate X (Nom)	515
Chromaticity Coordinate Y (Nom)	418
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	112.5 lm/W
Color rendering index (CRI)	21

  

Operating and Electrical	
Power Consumption	401.5 W
Lamp Current (Nom)	4.6 A
Voltage (Nom)	100 V

  

Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED18

  

Approval and Application	
Mercury (Hg) Content (Nom)	47 mg

  

Product Data	
Order product name	37688-9 400W C400S51/2 Dual Arc Hp Lamp
Full product name	37688-9 400W C400S51/2 Dual Arc Hp Lamp
Order code	928601145401
Material Nr. (12NC)	928601145401
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.010 kg
EAN/UPC - Product/Case	046677376888
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677376883

# Ceramalux Instant Restrike

## Dimensional drawing

Product	D	C (max)
37688-9 400W C400S51/2 Dual Arc Hp Lamp	2.25 inch	9.75 inch

