

## Utility Box 1.88 Inches Deep, 14 Cubic Inches, With Knockout, 2020BAR

By TradeSelect  
Catalog # 2020BAR



Utility Box, 1-7/8 in. Deep, 14 Cu. In., with Raised Ground Screw, 1/2 in. KO (50-Pack).

### Features

Utility Box 1.88 Inches Deep, 14 Cubic Inches, With Knockout

### Application

Utility boxes are used for convenience outlets, switch boxes or small junction boxes. They are popular for exposed work applications (surface mounted wiring).

### General

Bracket Type	No Bracket
Catalog Number	2020BAR
Drawn or Welded	Drawn
Gangable	No
Knockouts	10 x 1/2 in
Knockouts - Bottom	2 x 1/2in
Knockouts - End	2 x 1/2in
Knockouts - Side	6 x 1/2in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Sub Brand	tradeSELECT

Type	Handy Box, Box
UPC	626463001509
Wiring System	Conduit

### Dimensions

Actual Depth	1.875 in
Raised Ground	Yes
Weight	0.38 lb

### Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

### Logistics

Carton Quantity	50
Pallet Quantity	3500

### Product Assets

- [3D Product View - 2020](#)
- [Sales Drawings - 2020BAR](#)
- [Specifications - 2020BAR Specification Sheet French](#)