

Masonry Box, 3-1/2 In. Deep, 42 Cu. In., 2-Gang Masonry Box, 3-13/16 In. Width, 3-3/4 Height, Raised Ground Screw, With Concentric, 1/2 & 3/4 In. Ko (10-Pack)., MBD2K



By TradeSelect
Catalog # [MBD2K](#)

Masonry Box, 3-1/2 in. Deep, 42 Cu. In., 2-Gang Masonry Box, 3-13/16 in. Width, 3-3/4 Height, Raised ground screw, with Concentric, 1/2 & 3/4 in. KO (10-Pack).

Application

Masonry boxes are used for the flush installation of devices in masonry construction.

General

Bracket Type	No Bracket
Catalog Number	MBD2K
Drawn or Welded	Welded
Gangable	No
Knockouts	19 x 1/2-3/4 in Combination, 1 x 1/2-3/4-1 in Combination
Knockouts - Bottom	4 x 1/2-3/4in Combination
Knockouts - End	7 x 1/2-3/4in Combination, 1 x 1/2-3/4-1in Combination
Knockouts - Side	8 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	2-Gang
Plaster Ears	No
Sub Brand	tradeSELECT
Type	Masonry Box, Box

UPC	626463002681
Wiring System	Conduit

Dimensions

Actual Depth	3.516 in
Raised Ground	Yes
Weight	1.12 lb

Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	10
Pallet Quantity	750

Product Assets

- [3D Product View - MBD2K](#)
- [Specifications - MBD2K Specification Sheet French](#)