

## 4 In. Square Steel Stud Box, 2-1/8 In. Deep, 30 Cu. In., With Msb Metal Stud Bracket, For 2-3/8 And 3-5/8 In. Stud Size, (20-Pack), 52171MSB

By TradeSelect  
Catalog # [52171MSB](#)



4 In. Square Steel Stud Box, 2-1/8 in. Deep, 30 Cu. In., with MSB Metal Stud Bracket, for 2-3/8 and 3-5/8 in. Stud Size, with Concentric and 1/2 in. KO, Raised Ground Screw (20-Pack).

### Application

Steel stud boxes are used in Commercial, Residential and Industrial construction.

### General

Bracket Setback	0.4375
Bracket Type	MSB, for Steel Stud
Catalog Number	52171MSB
Drawn or Welded	Drawn
Gangable	No
Knockouts	6 x 1/2 in, 5 x 1/2-3/4 in Combination
Knockouts - Bottom	2 x 1/2in, 2 x 1/2-3/4in Combination
Knockouts - End	4 x 1/2in, 2 x 1/2-3/4in Combination
Knockouts - Side	1 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	2-Gang
Plaster Ears	No
Sub Brand	tradeSELECT

Type	Square Box, Box
UPC	626463003343
Wiring System	Conduit

### Dimensions

Actual Depth	2.125 in
Raised Ground	Yes
Weight	0.61 lb

### Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

### Logistics

Carton Quantity	20
Pallet Quantity	700

### Product Assets

- [3D Product View - 52171MSB](#)
- [Sales Drawings - 52171MSB](#)
- [Specifications - 52171MSB Specification Sheet French](#)