

HUBBELL Premise Wiring

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 15' Length, Blue

By Hubbell Premise Wiring
Catalog # [HC6AB15](#)



Copper Solutions, Ascent Patch Cord Cat 6A, Slim, 15'.

Features

- Third Party Verified Category 6A Component
- Plug Optimized For High Density Switch Ports
- 10-Gigabit Application Assurance
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6AB15
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	<ul style="list-style-type: none">• Conductor - 26AWG UTP• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating• Jacket - Dual Layer Flame-Retardant PVC - CM Rated• Plug Body - Polycarbonate UL 94V-0• Plug Boot - Polycarbonate UL 94V-0
Temperature Rating	Par TIA

UPC 662620229003

Dimensions

Length 15 ft
Outside Diameter 0.218

Electrical Ratings

Voltage Rating 300V AC kV

Conductor Related

Conductor Stranding Stranded
Conductor Type Copper
Number of Conductors 8-Conductor
Wire Size #24 AWG

Certifications And Compliance

Industry Standard(s)

- ANSI/TIA/EIA-568-C.2 Category 6A Component
- ISO 11801/60603-7-41 Category 6A Component

Logistics

Carton Quantity 20
Pallet Quantity 960

Product Assets

[Catalog Page - PREM D3 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - HC6AB15 Specification Sheet French](#)