

HUBBELL Premise Wiring

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 20' Length, Blue

By Hubbell Premise Wiring
Catalog # [HC6AB20](#)



Copper Solutions, Ascent Patch Cord Cat 6A, Slim, 20'.

Features

- Third Party Verified Category 6A Component
- Plug Optimized For High Density Switch Ports
- 10-Gigabit Application Assurance
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6AB20
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	<ul style="list-style-type: none">• Conductor - 26AWG UTP• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating• Jacket - Dual Layer Flame-Retardant PVC - CM Rated• Plug Body - Polycarbonate UL 94V-0• Plug Boot - Polycarbonate UL 94V-0

Temperature Rating UPC	Par TIA 662620229010
---------------------------	-------------------------

Dimensions

Length	20 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/TIA/EIA-568-C.2 Category 6A Component• ISO 11801/60603-7-41 Category 6A Component
----------------------	---

Logistics

Carton Quantity	15
-----------------	----

Product Assets

[Catalog Page - PREM D3 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - HC6AB20 Specification Sheet French](#)