

HUBBELL Premise Wiring

Patch Cord, Speed Gain, Cat6, Slim, White, 3'

By Hubbell Premise Wiring
Catalog # [HC6W03](#)



Patch Cord, Speed Gain, Cat6, Slim, White, 3'.

Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6W03
Color	White
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	<ul style="list-style-type: none">• Conductor - 24AWG UTP• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating• Jacket - Flame-Retardant PVC-CM Rated• OD - 0.224 in.• Plug Body - Polycarbonate UL 94V-0• Plug Boot - Polycarbonate UL 94V-0

Temperature Rating
UPC

Par TIA
662620233567

Dimensions

Length 3 ft
Outside Diameter 0.218

Electrical Ratings

Voltage Rating 300V AC kV

Conductor Related

Conductor Stranding Stranded
Conductor Type Copper
Number of Conductors 8-Conductor
Wire Size #24 AWG

Certifications And Compliance

Industry Standard(s)

- ANSI/TIA/EIA-568-C.2 Category 6 Component
- ISO 11801/60603-7-41 Category 6 Component

Logistics

Carton Quantity 65

Product Assets

[Catalog Page - PREM D5 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - HC6W03](#)