

Patch Cord, Speed Gain, Cat5E,  
Slim, White, 3' Length

By Hubbell Premise Wiring  
Catalog # [HC5EW03](#)



Patch Cord, Speed Gain, Cat5E, Slim, White, 3' Length.

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

|                       |                                                                                                                                                                                                                                                       |
|-----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Attenuation           | .1dB                                                                                                                                                                                                                                                  |
| Boot Type             | PVC                                                                                                                                                                                                                                                   |
| Catalog Number        | HC5EW03                                                                                                                                                                                                                                               |
| Color                 | White                                                                                                                                                                                                                                                 |
| EU RoHS Indicator     | Yes                                                                                                                                                                                                                                                   |
| Item Type             | NEXTSPEED Category 6 and 5e Patch Cords                                                                                                                                                                                                               |
| Material - Insulation | Flame Redardant PVC                                                                                                                                                                                                                                   |
| Material - Jacket     | Flame Redardant PVC                                                                                                                                                                                                                                   |
| Plug Type             | RJ45                                                                                                                                                                                                                                                  |
| Specifications        | <ul style="list-style-type: none"><li>• Conductor - 24AWG UTP</li><li>• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating</li><li>• Jacket - Flame-Retardant PVC-CM Rated</li><li>• Plug Body - Polycarbonate UL 94V-0</li></ul> |

Temperature Rating  
Type  
UPC

- Plug Boot - Polycarbonate UL 94V-0
- Per TIA  
Standard  
662620236490

Dimensions

|                  |       |
|------------------|-------|
| Length           | 3 ft  |
| Outside Diameter | 0.218 |

Electrical Ratings

|                |            |
|----------------|------------|
| Voltage Rating | 300V AC kV |
|----------------|------------|

Conductor Related

|                      |             |
|----------------------|-------------|
| Conductor Stranding  | Stranded    |
| Conductor Type       | Copper      |
| Number of Conductors | 8-Conductor |
| Wire Size            | #24 AWG     |

Certifications And Compliance

|                      |                                                                                                                                                   |
|----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• ANSI/TIA/EIA-568-C.2 Category 5E Component</li><li>• ISO 11801/60603-7-41 Category 5E Component</li></ul> |
|----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|

Product Assets

[Specifications - HC5EW03](#)