

# HUBBELL Premise Wiring

## Patch Cord, Speed Gain, Cat5E, Slim, White, 5'

By Hubbell Premise Wiring  
Catalog # [HC5EW05](#)



Patch Cord, Speed Gain, Cat5E, Slim, White, 5'.

### Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

### Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

### General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EW05
Color	White
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	<ul style="list-style-type: none"><li>• Conductor - 24AWG UTP</li><li>• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating</li><li>• Jacket - Flame-Retardant PVC-CM Rated</li><li>• Plug Body - Polycarbonate UL 94V-0</li></ul>

Temperature Rating  
Type  
UPC

- Plug Boot - Polycarbonate UL 94V-0
- Per TIA  
Standard  
662620236506

### Dimensions

Length  
Outside Diameter

5 ft  
0.218

### Electrical Ratings

Voltage Rating  
300V AC kV

### Conductor Related

Conductor Stranding  
Conductor Type  
Number of Conductors  
Wire Size

Stranded  
Copper  
8-Conductor  
#24 AWG

### Certifications And Compliance

Industry Standard(s)

- ANSI/TIA/EIA-568-C.2 Category 5E Component
- ISO 11801/60603-7-41 Category 5E Component

### Product Assets

[Specifications - HC5EW05](#)