

Patch Cord, Speed Gain, Cat5E,
Slim, White, 10'

By Hubbell Premise Wiring
Catalog # [HC5EW10](#)



Patch Cord, Speed Gain, Cat5E, Slim, White, 10'.

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EW10
Color	White
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	• Conductor - 24AWG UTP • Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating • Jacket - Flame-Retardant PVC-CM Rated • Plug Body - Polycarbonate UL 94V-0

Temperature Rating
Type
UPC

- Plug Boot - Polycarbonate UL 94V-0
- Per TIA
Standard
662620236520

Dimensions

Length
Outside Diameter

10 ft
0.218

Electrical Ratings

Voltage Rating

300V AC kV

Conductor Related

Conductor Stranding
Conductor Type
Number of Conductors
Wire Size

Stranded
Copper
8-Conductor
#24 AWG

Certifications And Compliance

- Industry Standard(s)
- ANSI/TIA/EIA-568-C.2 Category 5E Component
 - ISO 11801/60603-7-41 Category 5E Component

Product Assets

[Specifications - HC5EW10](#)