

HUBBELL Premise Wiring

Fiber Optic Pigtail, LC Multi Mode, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FPLCC3MM](#)



Fiber Optic Pigtail, LC Multi Mode, 3 Meter Length.

Application

LC

General

Catalog Number	FPLCC3MM
Connector Type	LC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620846040

Dimensions

Display Size	62.5 Micron, OM1
--------------	------------------

Length (Meters)	3 m
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OM1, MM
Wire Type	Multimode

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Specifications - FPLCC3MM Specification Sheet French](#)