

HUBBELL

Premise Wiring

Fiber Optic Pigtail, SC Single Mode, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FPSCS3SM](#)



Fiber Optic Pigtail, SC Single Mode, 3 Meter.

Application

SC

General

| | |
|--------------------|---|
| Catalog Number | FPSCS3SM |
| Connector Type | SC |
| EU RoHS Indicator | Yes |
| Insulation | PVC |
| Item Type | OptiChannel Fiber Pigtails, Single and Bundled |
| Material | Glass Fiber |
| Temperature Rating | 0 Degrees C to 75 Degree C |
| UPC | 662620837697 |

Dimensions

| | |
|--------------|---------|
| Display Size | SM, OS2 |
|--------------|---------|

| | |
|-----------------|-----|
| Length (Meters) | 3 m |
| Pitch | 6 |

Electrical Ratings

| | |
|--------------|---------|
| Connectivity | Plug-In |
|--------------|---------|

Conductor Related

| | |
|-----------|------------|
| Mode | OS2, SM |
| Wire Type | Singlemode |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 50 |
|-----------------|----|

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Specifications - FPSCS3SM Specification Sheet French](#)