

# HUBBELL Premise Wiring

## Fiber Optic Pigtail, LC Single Mode, 3) Meter Length

By Hubbell Premise Wiring  
Catalog # [FPLCS3SM](#)



Fiber Optic Pigtail, LC Single Mode, Three Meter.

### Application

LC

### General

Catalog Number	FPLCS3SM
Connector Type	LC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620846064

### Dimensions

Display Size	SM, OS2
--------------	---------

Length (Meters)	3 m
Pitch	6

### Electrical Ratings

Connectivity	Plug-In
--------------	---------

### Conductor Related

Mode	OS2, SM
Wire Type	Singlemode

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

[Brochures - Fiber Connectivity Product Guide](#)  
[Specifications - FPLCS3SM Specification Sheet French](#)