

HUBBELL Premise Wiring

Patch Cord, 10Gig, PC6A, Blue, 3' Length

By Hubbell Premise Wiring
Catalog # [PC6AB03](#)



Patch Cord, 10Gig, PC6A, Blue, 3' Length.

Features

- 10GbE Application Assurance
- Maximum Bandwidth Beyond 625MHz
- Component Compliant ANEXT Performance
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	PC6AB03
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	<ul style="list-style-type: none">• Conductor - 26AWG FTP• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating• Jacket - Flame-Retardant PVC-CM Rated• Plug Body - Polycarbonate UL 94V-0• Plug Boot - PVC

Temperature Rating
UPC

Par TIA
662620203997

Dimensions

Length
Outside Diameter

3 ft
0.218

Electrical Ratings

Voltage Rating
300V AC kV

Conductor Related

Conductor Stranding
Conductor Type
Number of Conductors
Wire Size

Stranded
Copper
8-Conductor
#24 AWG

Certifications And Compliance

Industry Standard(s)

- ANSI/TIA/EIA-568-C.2
Category 6A Component
- ISO 11801/60603-7-41
Category 6A Component

Logistics

Carton Quantity
200

Product Assets

[Catalog Page - PREM D4 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)