NetKey® Category 6 UTP Patch Cords

North America, Latin America, Europe, Middle East, Africa



SPECIFICATIONS

Category 6/Class E patch cords shall be constructed of UTP 24 AWG stranded copper cable and a modular plug at each end. Patch cords shall be used in all work area outlets and patch panels. Patch cords shall be wired to be compatible with both T568A and T568B wiring schemes.



TECHNICAL INFORMATION

Category 6/Class E channel performance:	Exceeds ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E channel requirements at swept frequencies up to 250 MHz Meets ANSI/TIA-568.2-D and ISO 11801 Category 6 component requirements at swept frequencies up to 250 MHz◊
Cable diameter:	0.235 in. (6.0mm) nominal
FCC compliance:	Complies with ANSI/TIA-1096-A (formerly FCC Part 68); contacts plated with 50 microinches of gold
IEC compliance:	Meets IEC 60603-7
PoE compliance:	Supports IEEE 802.3af/802.3at and 802.3bt type 3 and type 4 PoE applications
Safety compliance:	cULus Listed; UL 1863 and CAN/CSA-C22.2 (UL File E129886)
RoHS compliance:	Compliant
Flammability rating:	CM rated

KEY FEATURES AND BENEFITS

100% Performance tested:	Confidence that each patch cord delivers specified performance
Patented tangle-free latch:	Prevents snags and provides easy release
Slender strain relief boot:	Provides easy access in high-density applications
Identification:	Provides identification of performance level, length, and quality control number for future traceability

APPLICATIONS

Applications include:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), and 1000BASE-T (Gigabit Ethernet))
- 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM
- Token Ring 4/16
- Voice over internet protocol (VoIP)

NetKey Category 6 Patch Cords

Foot lengths: NK6PC*^Y
Meter lengths: NK6PC**M^Y

*Feet lengths: 1 – 20, 25, 30, 35, 40, 45, 50 feet


**Meter lengths: 1 – 5, 7, 10, 15, 20 meters

^Colors other than Off White: BU (Blue),
BL (Black), RD (Red), YL (Yellow), GY (Gray),
GR (Green), OR (Orange), VL (Violet)

^Lengths 1 meter to 15 meters or 1 foot to
49 feet are guaranteed to meet TIA and
ISO component and channel requirements.
Lengths greater than 15 meters or 49 feet
are guaranteed to meet ISO component and
both TIA and ISO channel requirements.

NetKey® Category 6 UTP Patch Cords

ENGINEERING DRAWING



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

