

LEVELS



LASER LEVELS

Self-leveling, easy-to-read horizontal & vertical laser lines

Projects horizontal and vertical lines independently or together for various alignments

Integrated magnetic 360° mounting bracket with 1/4" and 5/8" (0.6 cm and 1.6 cm) tripod mounting threads

IP54: water and dust resistant

Plumb spot lasers to pinpoint overhead locations

Mounting Bracket mount to ferromagnetic surfaces

X-Plane Laser
Z-Plane Laser
Y-Plane Laser

1/4-20 tripod mounting threads

Self-Leveling Cross-Line Laser Level with Red Plumb Spot

Includes core Laser Level features plus:

- High-performance laser leveling and alignment tool for professionals that provides a reliable self-leveling pendulum
- Horizontal and vertical laser lines and red plumb spot lasers that project horizontal and vertical lines independently or together to address various alignment tasks
- Integrated magnetic 360° mounting bracket with 1/4" and 5/8" (0.6 cm and 1.6 cm) tripod mounting threads
- Low battery indicator and easily accessible battery compartment
- Hard plastic carrying case included



Cat. No.	Laser Color	Accuracy	Overall Height	Overall Width	Overall Length
93LCLG	Cross-Line: Green; Plumb: Red	±3/32" per 33' (±2 mm per 10 m) Vertical & Horizontal Beams, ±1/8" per 33' (±3 mm per 10 m) Plumb Up Spot, ±5/32" per 33' (±4 mm per 10 m) Plumb Down Spot	5" (12.7 cm)	2.6" (6.6 cm)	5.3" (13.5 cm)
93LCLS	Cross-Line: Red; Plumb: Red	±3/32" per 33' (±2 mm per 10 m) Vertical & Horizontal Beams, ±1/8" per 33' (±3 mm per 10 m) Plumb Up Spot, ±5/32" per 33' (±4 mm per 10 m) Plumb Down Spot	5" (12.7 cm)	2.6" (6.6 cm)	5.3" (13.5 cm)

Rechargeable Self-Leveling Green Planar Laser Level

- Rechargeable Self-Leveling Green Planar Laser Level has easy-to-read high visibility green horizontal and vertical laser lines
- Projects independently or together in X-, Y- and Z-planes for various layout and alignment options
- View the upward and downward plumb marks at the intersection of the Y-plane and Z-plane
- More than 9 hour run time with integrated rechargeable Li-Ion battery
- Integrated magnetic mounting bracket with 1/4-20 tripod mounting threads
- Rugged body provides IP54 water and dust resistance
- Includes Li-Ion battery pack, USB-A to USB-C charging cable, magnetic mounting bracket, protective hard carrying case, and instructions



Cat. No.	Laser Color	Accuracy	Overall Height	Overall Width	Overall Length
93PLL	Cross-Line: Green	±11/64" per 33' (±4.5 mm per 10 m)	3.5" (1.4 cm)	4.8" (1.9 cm)	5.5" (2.2 cm)

