

Project Name

Location

Prepared By



## NUVO 65-996

LED 2 HEAD SECURITY FLOOD

**Notes**

(www) 1040-0004 00-00-01

**General**

Status	Active
Finish	Black
Wattage	17W/25W
Lumen Output	2190L-3352L
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Soft White to Natural Light
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

**Specifications**

Technology	LED
CRI	80+
Voltage	120V
Beam Angle	103
Rated Hours	50000
Operating Temperature	-30C (-22F) to +50C (+122F)
Photocell or Sensor	Has Photocell
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	1.25
Material	Die-Cast Aluminum

**Dimensions**

Height (in.)	4.41
Width (in.)	9.17
Extension (in.)	5.43

**Compliance**

Safety Listing	cULus - Certified
Location Rating	Wet
ADA Compliant	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

**Additional Information**

Additional Information	Powder Coated
Installation Notes	Mounts to Recessed or External Junction Boxes
Warranty	5 Year Limited - Fixtures