

Project Name

Location

Prepared By



Notes

(www) 10-02-2024 09:20:31

General

Status	Active
Fixture Type	Ceiling Wrap
Finish	White
Wattage	14W
Lumen Output	1298L-1391L
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Color Temperature	Warm White to Natural Light
CRI	90
Voltage	120V
Beam Angle	110
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Non-Dimmable
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	2.35
Material	Steel

Dimensions

Width (in.)	4.4
Length (in.)	18
Extension (in.)	2.51

Compliance

Safety Listing	cETLus
Location Rating	Damp
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	Tamper Resistant Dual GFCI Outlet with 15 amp circuit with 14 gauge wire; 0.025 second GFCI Trip Time; The outlet is front facing, It has an easy to read diagnostic indicator; Built in protection against shock; Most used application for this product would be a bathroom vanity
Installation Notes	Standard 3-inch and 4-inch Keyhole Slots
Warranty	5 Year Limited - Fixtures