

**2024 Specification Sheet - English**

---



**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Hassle-free, automatic measurement of amperage, voltage, and resistance. Low impedance eliminates stray or "ghost" voltage readings. Compact design for measuring in tight spaces. 400A AC, 600V AC/DC measurement

**PRODUCT NAME –**

---

**Page Title**

Automatic Electrical Tester, 600V, 400A

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Hassle-free, automatic measurement of amperage, voltage, and resistance

**Marketing Text 2**

Low impedance eliminates stray or "ghost" voltage readings

**Marketing Text 3**

Compact design for measuring in tight spaces

**Marketing Text 4**

400A AC, 600V AC/DC measurement

### **Marketing Text 5**

Data hold to capture important readings

### **Marketing Text 6**

Auto off for longer battery life

### **Marketing Text 7**

Accessories included: (1) 9 V battery, test leads, carrying case

### **Marketing Text 8**

Lifetime Limited Warranty

## **PRODUCT SPECIFICATION –**

---

### **Product Specification 1**

Amperage Measurement : 0.9 - 400.0A AC

### **Product Specification 2**

Display : LCD, 6000 Count

### **Product Specification 3**

Includes : (1) 9 V Battery, Test Leads, Carrying Case

### **Product Specification 4**

Jaw Opening : 1.060 IN

### **Product Specification 5**

Measurement Category : CAT III, 750/1000 VAC/DC

### **Product Specification 6**

CAT IV, 600 V

### **Product Specification 7**

Operation Type : Automatic

### **Product Specification 8**

Replacement Part : 11372 Test Leads, TC-5 Carrying case

### **Product Specification 9**

Resistance Measurement : 999 $\Omega$ , 9.999k $\Omega$

### **Product Specification 10**

Standard : CAT III, C/US UL Listed

### **Product Specification 11**

Type : Electrical

### **Product Specification 12**

Voltage Measurement : AC V: 1.3 - 600.0V

### **Product Specification 13**

DC V: 2.1 - 600.0; -0.7 TO -600.0V

