


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





PANDUIT P/N	WEIGHT
NMF1 NMF1WH	1.1 LBS/EACH 513 g/EACH



NOTES:

- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS:  
1- 1 RU MANAGER (FRONT ONLY)  
1- 1 RU 19" COVER
- DIMENSIONS IN PARENTHESES ARE METRIC.

MAX STORAGE TEMPERATURE 65° C (149° F)  
MAX OPERATING TEMPERATURE 60° C (140° F)



TITLE		<b>NMF1 CABLE MANAGER</b>		
		CUSTOMER DRAWING		
ITEM REVISION NAME		V10404AH/02		
DATASET FILE NAME		V10404AH_DC/02B		
		THIRD ANGLE PROJECTION		
MATERIAL		MANAGER: ABS 1RU COVER: PVC		DRAWING NUMBER 10404-15
REV	DATE	BY	CHK	SCALE
02B	4-29-20	JBO	JCO	JEFK
ADDED TEMPERATURE NOTE				
M09000LT				
REV	DATE	BY	CHK	APR
DESCRIPTION				
ECN				
		BAME		3-6-07
		TCK		NONE
		SHEET 1 OF 1		A

A-SIZE CUSTOMER