

Project Name

Location

Prepared By



NUVO 65-931

BULLET SEC LGT W/ CAM-BLA

Notes

(revised) 11-11-2024 00:16:01

General

Status	Active
Finish	Black
Wattage	20W
CCT (Kelvin)	3000K/4000K/5000K
Color Temperature	Soft White to Natural Light
Width (in.)	8.6
Height (in.)	6.31
Extension (in.)	7.32
Indoor or Outdoor Fixture	Outdoor

Smart Product Info

IOT Enabled	Yes
Integrated Camera	Yes
Operational Humidity	5% - 95%
Communication Protocol	WiFi-2.4GHz; 802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Voice Assistants Supported	Alexa; Google Home; Siri
Software Supported	Tuya/Starfish APP; AWS Cloud Security Servers
Storage Capacity	32GB SD Card Included; Optional 128GB Max SD Card

Specifications

Technology	LED
CRI	80
Lumen Output	1600L/1750L
Rated Hours	50000
Voltage	120V-277V
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Beam Angle	70
Operating Temperature	-20C (-4F) to +45C (+113F)
Weight (lb.)	1.43
Fixture Material	Die-Cast Aluminum / Plastic
Fixture Type	Security Camera

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	CCT Selectability is done via physical switch on unit at installation
Specification Note	3000K at 1600 Lumens; 4000K/5000K at 1750 Lumens
Installation Notes	Designed for Recessed or External Junction Boxes
Includes	Mounting hardware and accessories
Warranty	3 Year Limited - Fixtures