



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V GFCI Circuit Breakers - 1-Pole, GFCI - BLF, 10KAIC, 120VAC are Circuit Protection Molded Case Circuit Breakers. Sub Brand: N/A Type: BLF/GFCL Special Features: N/A Application: Electrical Distribution Standard: UL 943 Voltage Rating: 120V Amperage Rating: 30A Load Rating: N/A Frequency Rating: N/A Phase: N/A Frame: N/A Trip Type: N/A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 1P

General technical data	
number of poles	1
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	30 A
Model	
product brand name	Siemens
type of electrical connection	BOLT-ON
Mechanical Design	
depth [in]	1 in
design of the product	BLF/GFCL
height [in]	5 in
width [in]	4 in
General product approval	
standard	UL 943

last modified:

12/20/2023 

