



BEF15G1TN

By Burndy  
Catalog # [BEF15G1TN](#)

Tin Plated Ferrules.



General

|                                       |               |
|---------------------------------------|---------------|
| Catalog Number                        | BEF15G1TN     |
| Connector Type                        | Braid         |
| Material                              | Copper        |
| Material - Ferrules                   | Y             |
| Physical Attribute - Number of Braids | 2             |
| Plated                                | Y             |
| UPC                                   | 781810487600  |
| UPC 12 Digit                          | 7818104876000 |

Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 381 mm   |
| Dimension - Length Overall inch | 15.00 in |

Certifications And Compliance

|   |       |
|---|-------|
| Certification - CSA Approved            | No    |
| Certification - ETL                     | No    |
| Certification - UL Listed Direct Burial | No    |
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | CM    |
| UL Listed                               | No    |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - BEF15G1TN Specification Sheet French](#)