



BB139ML12T38TN, One-Hole Braid, 12" long, 3/8" stud, tin plated

By Burndy
Catalog # [BB139ML12T38TN](#)

One-Hole Braid, 139kcmil, 12", 3/8" stud, tin plated, approx AWG Size 2/0.



General

Catalog Number	BB139ML12T38TN
UPC	621945650961

Dimensions

Dimension - Stud Size inch	3/8"
Length	12 in
Thickness	0.16 in
Width	1.18 in

Conductor Related

Conductor Size	2/0 AWG
Wire Size	70mm ²

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section E2 - Mechanical Grounding](#)
[Literature - H3866CANEN \(1\)](#)
[Literature - H3867CANFR \(3\)](#)
[Sales Drawings - 50121367](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-BB139ML12T38TN-SPEC-EN | REV 6/2024