

## GC2929CG14

By Burndy

Catalog # [GC2929CG14](#)



### General

Catalog Number	GC2929CG14
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	N
UPC	621945013247
UPC 12 Digit	6219450132477

### Dimensions

Dimension - Height inch	2.08 in
Dimension - Height mm	52.8 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.59 in
Dimension - Thread Size	-
Dimension - Width fraction	1 in
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm

### Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
-------------------------------	-------------------------

Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2/0 AWG-250 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Y
Certification - UL Recognized	N
Certification - cULus	N
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - GC2929CG14 Specification Sheet French](#)