



B2D24D60G74TN

By Burndy  
Catalog # B2D24D60G74TN

Tin Plated Ferrules.



General

Catalog Number	B2D24D60G74TN
Connector Type	Braid
Material	Copper
UPC	781810567463
UPC 12 Digit	7818105674633

Dimensions

Dimension - D inch	1
Dimension - L Length Overall mm	625
Dimension - Length Overall inch	24.6
Dimension - N inch	0.5
Dimension - Pad Width inch	0.94

Electrical Ratings

Rating - Indoor Amperage	380
--------------------------	-----

Rating - Outdoor Amperage	455
---------------------------	-----

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - B2D24D60G74TN Specification Sheet French](#)