



BG24G106

By Burndy  
Catalog # BG24G106

Flexible Copper Braid.



General

Catalog Number	BG24G106
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	N
UPC	781810376232
UPC 12 Digit	7818103762322

Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in

Electrical Ratings

Rating - Indoor Amperage	415
Rating - Outdoor Amperage	495

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - BG24G106 Specification Sheet French](#)