



B4F16G8TN

By Burndy
Catalog # B4F16G8TN

Tin Plated Ferrules.



General

| | |
|---------------------------------------|---------------|
| Catalog Number | B4F16G8TN |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 4 |
| Plated | Y |
| UPC | 781810413579 |
| UPC 12 Digit | 7818104135799 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 406 mm |
| Dimension - Length Overall inch | 16.00 in |

Electrical Ratings

| | |
|---------------------------|------|
| Rating - Indoor Amperage | 1000 |
| Rating - Outdoor Amperage | 1200 |

Certifications And Compliance

| | |
|-------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance | EX |
| Status | |
| UL Listed | Yes |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B4F16G8TN Specification Sheet French](#)