



## BB139ML24T38TN, One-Hole Braid, 24" long, 3/8" stud, tin plated

By Burndy  
Catalog # [BB139ML24T38TN](#)

One-Hole Braid, 139kcmil, 24", 3/8" stud, tin plated, approx AWG Size 2/0.



### General

Catalog Number	BB139ML24T38TN
UPC	621945650985

### Dimensions

Dimension - Stud Size inch	3/8"
Length	24 in
Thickness	0.16 in
Width	1.18 in

### Conductor Related

Conductor Size	2/0 AWG
Wire Size	70mm <sup>2</sup>

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section E2 - Mechanical Grounding](#)  
[Literature - H3866CANEN \(1\)](#)  
[Literature - H3867CANFR \(3\)](#)  
[Sales Drawings - 50121367](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-BB139ML24T38TN-SPEC-EN | REV 6/2024