



BG12D93G102W

By Burndy
Catalog # BG12D93G102W

Tin Plated Ferrules.



General

Catalog Number	BG12D93G102W
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810349830
UPC 12 Digit	7818103498300

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	328 mm
Dimension - Length Overall inch	12.93 in
Dimension - Pad Width inch	1.50 in

Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BG12D93G102W Specification Sheet French](#)