



B2G60N

By Burndy
Catalog # B2G60N

Flexible Copper Braid.



General

Catalog Number	B2G60N
Connector Type	Braid
Material	Copper
UPC	781810225912

Dimensions

Dimension - L Length Overall mm	60
Dimension - Length Overall inch	1524

Electrical Ratings

Rating - Indoor Amperage	840 A
Rating - Outdoor Amperage	700 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30015322](#)
- [Specifications - B2G60N Specification Sheet French](#)