



## HSB34H48PF5, Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.22" ID Max. (Rec.), 6-2 AWG, Heavy Wall, Black, 4" Length

By Burndy  
Catalog # [HSB34H48PF5](#)



Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.22" ID Max.(Rec.), 6-2 AWG, Cross Linked Polyolefin, Heavy Wall, Flame Retardant, Black, 1000V, 4" Length.

### General

Application	For Direct Burial
Catalog Number	HSB34H48PF5
Connector Type	HEAVY WALL TUBES
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-H-PF, Heavy Wall, Flame Retardant
UPC	781810214893

### Conductor Related

Conductor Range	#6 AWG to #2 AWG
Conductor Size	6AWG - 2AWG

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	5
Number of Pieces in Package	5

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB35H6PF25\\_LineArt](#)
- [Sales Drawings - SD211942-01](#)
- [Video - Heat Shrink Product Overview & Installation](#)



A Hubbell brand