



B2F12D50G134SV

By Burndy
Catalog # B2F12D50G134SV

Flexible tinned copper braid 11.50"x1.50"x0.44".



General

Catalog Number	B2F12D50G134SV
Connector Type	Braid
Material	Copper
Material - Ferrules	Silver Plated Copper Ferrule
Physical Attribute - Number of Braids	2
UPC	781810548868
UPC 12 Digit	7818105488688

Dimensions

Dimension - L Length Overall mm	318
Dimension - Length Overall inch	12.5
Dimension - Width inch	1.38
Dimension - Width mm	35 mm

Electrical Ratings

Rating - Indoor Amperage	600 A
Rating - Outdoor Amperage	720 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B2F12D50G134SV Specification Sheet French](#)



A Hubbell brand